ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
10101 SH 30
College Station, TX 77845-0000
Phone: 9797796630
Fax: 9797796620



CS6364C CA STYL 50A 125/250V T/L CONN

PASS & SEYMOUR/LEGRAND

Catalog Number	CS6364C
Manufacturer	PASS & SEYMOUR/LEGRAND
Description	50A Turnlok Plugs and Connectors make installing and securing your connections faster, safer and more dependable than ever. These devices are designed to withstand harsh environments. Each device features a simple push, twist and lock body assembly for greater productivity and labor savings in temporary power applications. The back body easily slides onto the device and locks in place with a quarter twist making installations faster, safer and more dependable.
Weight per unit	1.0 (lbs/each)
Product Category	Conduit & Raceways

Features

Material	Nylon
Number Of Wires	4
Voltage	250.0 V

Material, Color, and Finish

Contact Material	Brass

Descriptions

Description	CA STYL 50A 125/250V T/L CONN
Features	50A Turnlok Plugs and Connectors make installing and securing your connections faster, safer and more dependable than ever. These devices are designed to withstand harsh environments. Each device features a simple push, twist and lock body assembly for greater productivity and labor savings in temporary power applications. The back body easily slides onto the device and locks in place with a quarter twist making installations faster, safer and more dependable.
Long Description	50A Turnlok Plugs and Connectors make installing and securing your connections faster, safer and more dependable than ever. These devices are designed to withstand harsh environments. Each device features a simple push, twist and lock body assembly for greater productivity and labor savings in temporary power applications. The back body easily slides onto the device and locks in place with a quarter twist making installations faster, safer and more dependable.
Product Type	Ca Styl 50A 125/250V T/L Conn
Special Features	CS6364C Locking Connector
Extra Long Description	PAS CS6364C CA STYL 50A 125/250V T/

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
10101 SH 30
College Station, TX 77845-0000
Phone: 9797796630
Fax: 9797796620

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007442465
Manufacturers Part Number	CS6364C
UPC	785007

Taxonomies, Classifications, and Categories

Category Description	Wire/Plug Strips, Surf Raceways, Power Pole, Walkerduct, & Plugmolds
Type	LOCKING CONNECTOR

Trade Size

Amperage	50.0

Packaging

Carton	1
Package	10
Weight Per Each	1.0 (lbs/each)

Uses, Certifications, and Standards

Standard	ROHS, CULUS, RoHS, UL UL498, cULus E146159

PASS & SEYMOUR®

50A Turnlok® Plugs and Connectors



CS6365C Plug & CS6364C Connector

Safe and Durable 50A Power Connections

Our 50A Turnlok Plugs and Connectors make installing and securing your connections faster, safer and more dependable than ever. These devices are designed to withstand harsh environments. 50A Turnlok Plugs and Connectors feature a simple push, twist and lock body assembly for greater productivity and labor savings in temporary power applications. The back body easily slides onto the device and locks in place with a quarter twist making installations faster, safer and more dependable.

Features & Benefits

Feature:

- Quality Materials, durability, and time-tested design.
- Push, twist and lock design that eliminates the need for time-consuming threading
- Industrial-Strength Brass Alloy Plug Blades and Connector Contacts: Resist heat rise and provide excellent conductivity.
- Nylon 66 shell material is impact and UV-resistant
- Features an adjustable cord clamp strategically located outside the back body to accommodate various cord sizes
- Device's same-plane hex terminations make every termination faster and safer
- Integral flexible rubber cord grommet provides protection from oils, water or chips entering the wiring chamber

Vertical Markets

- **Construction Sites**
- **Outdoor Events**
- **Entertainment Venues**
- **Disaster Relief**
- **Data Center**

Compliance

cULus Listed Wiring Assembly: File E146159.
Standard UL498 Attachment Plugs and Receptacles

Technical Information

Performance	
Electrical	
Dielectric Withstand Voltage	Withstands 3000V
Number of Wires	3/4
Number of Poles	2/3
Frequency	60 Hz
Voltage Range	125-600V

Mechanical	
Terminal Identification	“GR” and Green color = Ground, “WH” and White color = Neutral, “X”, “Y”, “Z” = Hot
Terminal Accommodation	#8 AWG min. - #4 AWG max.
Product Identification	Amperage, Voltage, 3rd Party Compliance, hot stamped onto device

Environmental	
Operating Temperature	Maximum continuous +75°C, minimum -40°C without impact
Maximum Humidity	95%
Flammability	UL94 V2


Material Specs	
Face	Nylon 66
Body	Nylon 66
Contacts	.05” Brass
Mounting Strap	Galvanized Steel
Terminal Screws	Nickel-Plated Steel #5/16 – 24

Warranty

1 Year

Ordering Information

Catalog No./Item	Ratings A.	Ratings V.	Description/Color	Cord Diameter
Connectors California Standard				
CS6360C	50A	125V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS6364C	50A	125/250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8164C	50A	3ø480V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8264C	50A	250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8364C	50A	3ø250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8464C	50A	480V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
Plugs California Standard				
CS6361C	50A	125V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS6365C	50A	125/250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8165C	50A	3ø480V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8265C	50A	250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8365C	50A	3ø250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8465C	50A	480V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
Connectors Corrosion Resistant				
CR6360C	50A	125V	Yellow Back, White Front Body	.700"-1.200" 8AWG-4AWG
CR6364C	50A	125/250V	Yellow Back, White Front Body	.700"-1.200" 8AWG-4AWG
Plugs Corrosion Resistant				
CR6361C	50A	125V	Yellow Back, White Front Body	.700"-1.200" 8AWG-4AWG
CR6365C	50A	125/250V	Yellow Back, White Front Body	.700"-1.200" 8AWG-4AWG
Connectors 50A Turnlok				
3762C	50A	600VAC/250VAC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
3764C	50A	600VAC/250VDC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
7764C	50A	600VAC/250VDC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
Plugs 50A Turnlok				
3763MC	50A	600VAC/250VAC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
3765C	50A	600VAC/250VDC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
7765C	50A	600VAC/250VDC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG



All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
877-295-3472
www.legrand.us

Canada
844-977-3783
www.legrand.ca

FOLLOW US

CS3314 — April 2024 — For latest specs visit www.legrand.us/passandseymour

©2024 Legrand All Rights Reserved