



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2703 Hancock Dr.  
76504-0000, TX Temple  
Phone: 254-899-2800  
Fax: 254-899-2805



## CSB20AC1GRY 20A 120/277VAC B+S Wire Comm SP SW Gy

*Pass & Seymour/Legrand*

Catalog Number	CSB20AC1GRY
Manufacturer	Pass & Seymour/Legrand
Description	Construction 1-Pole Switch, Back and Side-Wire, 20A 120/277V.
Weight per unit	0.1692 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	SP
actuator	Toggle
amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	LED, Halogen, Incandescent, Xenon, Universal, Fluorescent, CFL
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	20A 120/277VAC B+S WIRE COMM SP SW GY
extra long description	P&S CSB20AC1GRY 20A 120/277VAC B+S
Features	Single Piece Plated Steel Mounting Strap
Long Description	Construction 1-Pole Switch, Back and Side-Wire, 20A 120/277V.
Product Type	20A 120/277VAC B+S Wire Comm SP SW Gry
Special Features	Back & Side wire, locking support, one piece brass alloy contact arm



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2703 Hancock Dr.  
76504-0000, TX Temple  
Phone: 254-899-2800  
Fax: 254-899-2805

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126068
Manufacturers Part Number	CSB20AC1-GRY
UPC	785007126068

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.1692

## Uses, Certifications, and Standards

Application	Commercial/Residential
Mounting standard	WALL CULUS, UL20, FEDSPEC