



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253



CSB20AC2GRY 20A 120/277VAC B+S Wire Comm DP SW Gy

Pass & Seymour/Legrand

Catalog Number	CSB20AC2GRY
Manufacturer	Pass & Seymour/Legrand
Description	Construction 2-Pole Switch, Back and Side-Wire, 20A 120/277V.
Weight per unit	0.1872 (lbs/each)
Product Category	Gen Purpose Switches

Features

amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Incandescent, Fluorescent, LED, CFL, Xenon, Universal, Halogen
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	2
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	2
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	20A 120/277VAC B+S WIRE COMM DP SW GY
extra long description	P&S CSB20AC2GRY 20A 120/277VAC B+S
Features	Single Piece Plated Steel Mounting Strap
Long Description	Construction 2-Pole Switch, Back and Side-Wire, 20A 120/277V.
Product Type	20A 120/277VAC B+S Wire Comm DP SW Gry
Special Features	High strength toggle, heavy duty toggle bumpers, locking support



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007126167
Manufacturers Part Number	CSB20AC2-GRY
UPC	785007126167

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.1872

Uses, Certifications, and Standards

Application	Commercial
Mounting standard	WALL CULUS, UL 20, FEDSPEC