



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CSB20AC2W 20A 120/277VAC B+S Wire Comm DP SW WH

*Pass & Seymour/Legrand*

Catalog Number	CSB20AC2W
Manufacturer	Pass & Seymour/Legrand
Description	Toggle Switch, 2 Poles, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, White, Grounding Connection, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.19 LB
Weight per unit	0.1872 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	Double pole
actuator	Toggle
amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Fluorescent, Xenon, Universal, Halogen, LED, Incandescent, CFL
Number of Gangs	1
Number of Switches	1.0
Poles	2
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	20A 120/277VAC B+S WIRE COMM DP SW WH
extra long description	P&S CSB20AC2W 20A 120/277VAC B+S WI



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126198
Manufacturers Part Number	CSB20AC2W
UPC	785007126198

## Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.1872

## Uses, Certifications, and Standards

Enclosure	Nylon
Mounting standard	WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC