



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CSD363012SS 36X30X12 N4X SS4 HC, QTR TRN LTCH

*Hoffman Enclosures, Inc.*

Catalog Number	CSD363012SS
Manufacturer	Hoffman Enclosures, Inc.
Description	Concept Wallmount 1/4-Turn Latch Type 4X, 36X30X12, Brushed, Stainless 304
Weight per unit	88.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

ip rating	IP66
Material	Stainless Steel 304

### Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4
Style	Quarter-turn

### Dimensions and Weight

Depth	12
Height	36
Size	36.00x30.00x12.00 in
Width	30

### Descriptions

Description	36X30X12 N4X SS4 HC, QTR TRN LTCH
extra long description	NVENT HOF CSD363012SS Wall-Mount Ty
Features	For indoor or outdoor applications that require corrosion protection from chemicals and water. Concept Enclosures feature streamlined styling with an attractive stroked finish and flush quarter-turn latches for secure closure.
Long Description	Concept Wallmount 1/4-Turn Latch Type 4X, 36x30x12, Brushed, Stainless 304
Product Type	Wall-Mount Type 4X Enclosure

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510488604
Manufacturers Part Number	CSD363012SS
UPC	783510488604

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	88

## Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X Watertight, corrosion-resistant