



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Veterans Avenue
75672-0000, TX Marshall
Phone: 903-935-9535
Fax: 903-935-3490



CTAPF212C Comp C-Tap *Panduit Corporation*

Catalog Number	CTAPF212C
Manufacturer	Panduit Corporation
Description	C-Type Copper Compression Tap, #4 Awg (Run and Tap);25 SQ.MM (Run and Tap);#3 Awg (Run);25 SQ.MM (Run);#5 Awg (Tap);16 SQ.MM (Tap);#2 Awg (Run);35 SQ.MM (Run);#12-#6 Awg (Tap);4-16 SQ.MM (Tap) Conductor Size, Non-Insulated, Copper Conductor Material, Pink (Code) Insulation Color, +90 °C Operating Temperature, 1.25 In Overall Length, Compression Terminal, 600 V
Weight per unit	3.7 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
media	Yes

Material, Color, and Finish

Clamp Material	Copper
Color	Brown

Dimensions and Weight

Length	1.25
--------	------

Descriptions

Description	COMP C-TAP
extra long description	PAN CTAPF2-12-C StructuredGround™ C

Manufacturer Information

Brand	PANDUIT
GTIN	00074983599752
UPC	074983599752

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Compression Tap

Packaging

Carton	100
Weight Per each	3.72

Uses, Certifications, and Standards

Application	Utility/Ground Grid
standard	UL listed and CSA certified to 600 V