


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

CATALOG NUMBER	STRANDED COPPER CONDUCTOR SIZE (AWG)		NO. OF RIBS	DIMENSIONS				COLOR CODE	WIRE STRIP LENGTH	INSTALLATION TOOLING PANDUIT DIE PART NO. DIE SET COLOR & INDEX NO. NO OF CRIMPS ( )			
	RUN	TAP		A +/- .02 [.5]	Q +/- .01 [.3]	T (MATERIAL THICKNESS) + .01 [.3]	V +/- .01 [.3]			CT-2001	CT1700**	CT-920, CT-920CH, CT2920, CT-930, CT-930CH CT-940CH*, CT-2940*	
CTAFF10-16TP-C	14	16-14	0	.41	.13	.06	.19	RED	1/2" [12.7]	-----	CD-2001-8 RED P21 (1)	RED P21 (2)	-----
	12	16-12		[10.4]	[3.3]	[1.5]	[4.8]						
	10	14											
CTAFF8-12TP-C	10	10	0	.67	.19	.07	.26	BLUE	11/16 [17.5]	-----	CD-2001-6 BLUE P24 (1)	BLUE P24 (2)	-----
	8	12		[17.0]	[4.8]	[1.8]	[6.6]						
CTAFF6-12TP-C	8	10-8	0	.67	.24	.07	.32	GRAY	11/16 [17.5]	-----	CD-2001-4 GRAY P29 (1)	GRAY P29 (2)	-----
	6	12-10		[17.0]	[6.1]	[1.8]	[8.1]						
CTAFF4-12TP-C	6	8-6	1	1.25	.28	.07	.40	BROWN	1-5/16" [33.3]	CDM-2001-2 BROWN P33M (1)	CD-2001-2 BROWN P33 (2)	BROWN P33 (4)	CDM-920-2 BROWN P33M (1)
	5.4	12-8		[31.8]	[7.1]	[1.8]	[10.2]						
CTAFF3-12TP-C	5.4	6-5	1	1.25	.31	.08	.46	GREEN	1-5/16" [33.3]	CDM-2001-1 GREEN P37M (1)	CD-2001-1 GREEN P37 (2)	GREEN P37 (4)	CDM-920-1 GREEN P37M (1)
	3	12-6		[31.8]	[7.9]	[2.0]	[11.7]						
CTAFF2-12TP-C	4	4	1	1.25	.33	.08	.51	PINK	1-5/16" [33.3]	CDM-2001-1/0 PINK P42M (1)	CD-2001-1/0 PINK P42 (2)	-----	CDM-920-1/0 PINK P42M (1)
	3	5		[31.8]	[8.4]	[2.0]	[13.0]						
	2	12-6											
CTAFF1-12TP-C	3	4-3	2	1.82	.40	.08	.57	BLACK	1-7/8" [47.6]	CDM-2001-2/0 BLACK P45M (2)	CD-2001-2/0 BLACK P45 (3)	-----	CDM-920-2/0 BLACK P45M (1)
	2	5-4		[46.2]	[10.2]	[2.0]	[14.5]						
	1	12-5											
CTAFF1/0-12TP-L	2	4-2	2	1.82	.42	.09	.63	ORANGE	1-7/8" [47.6]	CDM-2001-3/0 ORANGE P50M (2)	CD-2001-3/0 ORANGE P50 (3)	-----	CDM-920-3/0 ORANGE P50M (1)
	1	4-3		[46.2]	[10.7]	[2.3]	[16.0]						
	1/0	12-4											
CTAFF2/0-12TP-Q	1	2-1	2	1.82	.48	.09	.71	PURPLE	1-7/8" [47.6]	-----	CD-2001-4/0 PURPLE P54 (3)	-----	CDM-920-4/0 PURPLE P54M (1)
	1/0	3-2		[46.2]	[12.2]	[2.3]	[18.0]						
	2/0	12-3											
CTAFF3/0-12TP-Q	1/0	1-1/0	2	1.82	.55	.09	.81	YELLOW	1-7/8" [47.6]	-----	CD-2001-250 YELLOW P62 (3)	-----	CDM-920-250 YELLOW P62M (1)
	2/0	2-1		[46.2]	[14.0]	[2.3]	[20.6]						
	3/0	12-2											



\* CT-940CH AND CT-2940 REQUIRE CD-940-DA ADAPTER FOR CDM-920 DIES  
 \*\* CT-1700 CRIMP DIE POCKETS ARE INTEGRATED INTO THE TOOL HEAD


NOTES:

- MATERIAL: COPPER, TIN PLATED
- UL LISTED AND CSA CERTIFIED FOR APPLICATIONS UP TO 600 VOLTS. TEMPERATURE RATING 90° C
- DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
- PACKAGE QUANTITY:  
 -C = 100  
 -L = 50  
 -Q = 25

							<b>PANDUIT CORP. TINLEY PARK, ILLINOIS</b>		
							NON-INSULATED THIN-WALL C-TAP CONNECTORS, TIN PLATED CUSTOMER DRAWING		
02	1/11	JHNU	JHNU	REVISED AGENCY LOGOS	N41731BB-C41731	FLD	FLD	UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
01	1/11	JHNU	JHNU	ADDED cULus, DB, & CSA LOGOS ADDED +/- .02 [.5] TOLERANCE TO DIMENSION A ADDED +/- .01 [.3] TOLERANCE TO DIMENSIONS Q, T, & V	N41731BB-C41731	FLD	FLD		
00	9/07	JHNU	JHNU	DRAWING RELEASED				DRAWN BY JHNU	SCALE NONE
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	DATE 9/07	DWG B SIZE
								SEE NOTE 1 ABOVE	DRAWING NO / CAD FILE C41731_02

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

CATALOG NUMBER	STRANDED COPPER CONDUCTOR SIZE (AWG)		NO. OF RIBS	DIMENSIONS				COLOR CODE	WIRE STRIP LENGTH	INSTALLATION TOOLING PANDUIT DIE PART NO. DIE SET COLOR & INDEX NO. NO OF CRIMPS ( )			
	RUN	TAP		A +/- .02 [.5]	Q +/- .01 [.3]	T (MATERIAL THICKNESS) + .01 [.3]	V +/- .01 [.3]			CT-2001	CT1700**	CT-920, CT-920CH, CT2920, CT-930, CT-930CH CT-940CH*, CT-2940*	
CTAFF10-16TP-C	14	16-14	0	.41 [10.4]	.13 [3.3]	.06 [1.5]	.19 [4.8]	RED	1/2" [12.7]	-----	CD-2001-8 RED P21 (1)	RED P21 (2)	-----
	12	16-12											
	10	14											
CTAFF8-12TP-C	10	10	0	.67 [17.0]	.19 [4.8]	.07 [1.8]	.26 [6.6]	BLUE	11/16 [17.5]	-----	CD-2001-6 BLUE P24 (1)	BLUE P24 (2)	-----
	8	12											
CTAFF6-12TP-C	8	10-8	0	.67 [17.0]	.24 [6.1]	.07 [1.8]	.32 [8.1]	GRAY	11/16 [17.5]	-----	CD-2001-4 GRAY P29 (1)	GRAY P29 (2)	-----
	6	12-10											
CTAFF4-12TP-C	6	8-6	1	1.25 [31.8]	.28 [7.1]	.07 [1.8]	.40 [10.2]	BROWN	1-5/16" [33.3]	CDM-2001-2 BROWN P33M (1)	CD-2001-2 BROWN P33 (2)	BROWN P33 (4)	CDM-920-2 BROWN P33M (1)
	5.4	12-8											
CTAFF3-12TP-C	5.4	6-5	1	1.25 [31.8]	.31 [7.9]	.08 [2.0]	.46 [11.7]	GREEN	1-5/16" [33.3]	CDM-2001-1 GREEN P37M (1)	CD-2001-1 GREEN P37 (2)	GREEN P37 (4)	CDM-920-1 GREEN P37M (1)
	3	12-6											
CTAFF2-12TP-C	4	4	1	1.25 [31.8]	.33 [8.4]	.08 [2.0]	.51 [13.0]	PINK	1-5/16" [33.3]	CDM-2001-1/0 PINK P42M (1)	CD-2001-1/0 PINK P42 (2)	-----	CDM-920-1/0 PINK P42M (1)
	3	5											
	2	12-6											
CTAFF1-12TP-C	3	4-3	2	1.82 [46.2]	.40 [10.2]	.08 [2.0]	.57 [14.5]	BLACK	1-7/8" [47.6]	CDM-2001-2/0 BLACK P45M (2)	CD-2001-2/0 BLACK P45 (3)	-----	CDM-920-2/0 BLACK P45M (1)
	2	5-4											
	1	12-5											
CTAFF1/0-12TP-L	2	4-2	2	1.82 [46.2]	.42 [10.7]	.09 [2.3]	.63 [16.0]	ORANGE	1-7/8" [47.6]	CDM-2001-3/0 ORANGE P50M (2)	CD-2001-3/0 ORANGE P50 (3)	-----	CDM-920-3/0 ORANGE P50M (1)
	1	4-3											
	1/0	12-4											
CTAFF2/0-12TP-Q	1	2-1	2	1.82 [46.2]	.48 [12.2]	.09 [2.3]	.71 [18.0]	PURPLE	1-7/8" [47.6]	-----	CD-2001-4/0 PURPLE P54 (3)	-----	CDM-920-4/0 PURPLE P54M (1)
	1/0	3-2											
	2/0	12-3											
CTAFF3/0-12TP-Q	1/0	1-1/0	2	1.82 [46.2]	.55 [14.0]	.09 [2.3]	.81 [20.6]	YELLOW	1-7/8" [47.6]	-----	CD-2001-250 YELLOW P62 (3)	-----	CDM-920-250 YELLOW P62M (1)
	2/0	2-1											
	3/0	12-2											



\* CT-940CH AND CT-2940 REQUIRE CD-940-DA ADAPTER FOR CDM-920 DIES  
 \*\* CT-1700 CRIMP DIE POCKETS ARE INTEGRATED INTO THE TOOL HEAD

- NOTES:
1. MATERIAL: COPPER, TIN PLATED
  2. UL LISTED AND CSA CERTIFIED FOR APPLICATIONS UP TO 600 VOLTS. TEMPERATURE RATING 90° C
  3. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
  4. PACKAGE QUANTITY:  
 -C = 100  
 -L = 50  
 -Q = 25

							<b>PANDUIT CORP. TINLEY PARK, ILLINOIS</b>		
							NON-INSULATED THIN-WALL C-TAP CONNECTORS, TIN PLATED CUSTOMER DRAWING		
02	1/11	JHNU	JHNU	REVISED AGENCY LOGOS	N41731BB-C41731	FLD	FLD	UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
01	1/11	JHNU	JHNU	ADDED cULus, DB, & CSA LOGOS ADDED +/- .02 [.5] TOLERANCE TO DIMENSION A ADDED +/- .01 [.3] TOLERANCE TO DIMENSIONS Q, T, & V	N41731BB-C41731	FLD	FLD		
00	9/07	JHNU	JHNU	DRAWING RELEASED				DRAWN BY JHNU	SCALE NONE
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	DATE 9/07	DWG B SIZE
								SEE NOTE 1 ABOVE	DRAWING NO / CAD FILE C41731_02