



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



D131RX 13 In 1 Ratcheting Screwdriver (Bulk)

L.H. Dottie CO.

| | |
|------------------|--|
| Catalog Number | D131RX |
| Manufacturer | L.H. Dottie CO. |
| Description | Ratcheting Screwdriver, 1/4 In. Tip Size, Hex Tip Type, Cushion Grip, Tapered Handle Type, Heavy Duty Nylon Handle Material, Red/Black Handle Color, 225 LB. Torque Strength, Bulk |
| Weight per unit | 0.6000 (lbs/each) |
| Product Category | Pliers, Wrenches, Saw, Pouches |

Features

| | |
|-------------|-----------------------|
| Handle Type | Cushion Grip, Tapered |
| Tip Size | 1/4 |
| tip type | Hex |

Material, Color, and Finish

| | |
|-----------------|------------------|
| Handle Color | RED/BLACK |
| Handle Material | Heavy Duty Nylon |

Descriptions

| | |
|------------------------|--|
| Description | 13 IN 1 RATCHETING SCREWDRIVER (BULK) |
| extra long description | DOTTIE D131RX 13 in 1 Ratcheting Sc |
| Long Description | Ratcheting Screwdriver, 1/4 in. tip size, Hex tip type, Cushion Grip, Tapered handle type, Heavy Duty Nylon handle material, Red/Black handle color, 225 lb. torque strength, Bulk |
| Product Type | 13 In 1 Ratcheting Screwdriver |
| Special Features | Features: Convenient Storage for a Wide Range of Bits, 1/4" Hex Driver Shaft - Great for 1/4" Hex Head Screws, Precision 28 Tooth Ratchet Makes Driving Fasteners Faster and Easier, Heavy Duty Nylon Reinforced Handle & Chamfered Solid Steel Shaft For Long |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | LH DOTTIE |
| GTIN | 00781002841753 |
| Manufacturers Part Number | D131RX |
| UPC | 781002841753 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | HAND TOOLS |
| Type | Ratcheting Screwdriver |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.6 |