



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## D250AC 1/4" Tab 2FML, 1ML DSCNCT Adptr *Panduit Corporation*

Catalog Number	D250AC
Manufacturer	Panduit Corporation
Description	The Vibration Resistant Disconnect Adapter In Metallic Brass Couples Two Female Tabs and One Male Tab All Sized At 0.250 X 0.032 (6.3 X 0.8 MM). The Adapter Is 0.82" (20.8 MM) Long and 0.57" (14.5 MM) Wide. It Tin-Plated, Non-Insulated, and Comes In Bottles Of 100.
Weight per unit	0.3600 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

insulation	None
Material	Brass
Voltage Rating	2000

### Material, Color, and Finish

Finish	Tinned
--------	--------

### Descriptions

Description	1/4" TAB 2FML,1ML DSCNCT ADPTR
extra long description	PAN D-250A-C Pan-Term® D-250A-C Loo
Long Description	The vibration resistant disconnect adapter in metallic brass couples two female tabs and one male tab all sized at 0.250 x 0.032 (6.3 x 0.8 mm). The adapter is 0.82" (20.8 mm) long and 0.57" (14.5 mm) wide. It tin-plated, non-insulated, and comes in bottles of 100.
Product Type	Pan-Term® D-250A-C Loose Piece Disconnect

### Manufacturer Information

Brand	Panduit®
GTIN	00074983827503
Manufacturers Part Number	D-250A-C
UPC	074983827503

### Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Disconnect

### Availability

minimum qty	100
-------------	-----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	100
Weight Per each	0.36

## Uses, Certifications, and Standards

Mounting	1932-09-01
Temperature Rating	266 Degrees Fahrenheit (130 Degrees Celsius)