




Dimmers & Fan Speed Controls Decorator Dimmers – Advanced Functionality

Tap down once for full Off. Hold paddle up to raise lights, down to lower.

Sleek, ergonomic P&S Decorator style matches other Decorator devices.




Red LED night light glows when Off.

Convenient operation – combines On/Off preset Decorator switch with separate slider microswitch for separate dimming control.


Soft start control brings lights up slowly, extends bulb life.

Constant memory returns lights to previous level after power failure.

D600-ELA



D600-ELA



D1000-ELA

NEW

NEW

NEW


Catalog Number	Description	Ratings	Color
600W Incandescent Decorator Dimmers*†			
D600-EW D600-EI D600-ELA	Mechanical Preset, Single Pole and 3-Way	600 Watt	White Ivory Light Almond
1000W Incandescent Decorator Dimmers*†			
D1000-EW D1000-EI D1000-ELA	Mechanical Preset, Single Pole and 3-Way	1000 Watt	White Ivory Light Almond
Decorator On/Off Remotes*†			
DR-EW DR-EI DR-ELA	Multilocation/3-Way		White Ivory Light Almond

* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: D600-ELAV.

† All dimmers and fan controls can be operated from more than one location when used with DRE remotes. Uses standard 3-way wiring. See wiring diagram.

WIRING DIAGRAMS

Single Pole and Multilocation




Dimmers & Fan Speed Controls

Constant memory returns lights to previous level after power failure.

Enables On/Off and full dimming control from an unlimited number of locations.

LED indicators keep you informed. Green LEDs indicate preset level and current light level. Red LED night light glows when load is off.

Easy operation — Tap up once for preset, twice for full On. Tap down once for full Off. Hold paddle up to raise lights, down to lower.



D600M-LAV

Sleek, ergonomic P&S Decorator style matches other Decorator devices.

Unobtrusive preset selection button helps prevent accidental setting changes.

Change light level without affecting preset.

Elegant fade On and Off extends bulb life. Easy on the eyes, too.

Installs easily using the same wiring as conventional 3-way switches.

Today's home and business owners want optimum control of their electrical systems. P&S Dimmers & Fan Speed Controls provide that control — along with aesthetics, durability, trouble-free installation, and technologies aimed at solving real-world problems.

Index

Device	Rating	Page Number
Catalog Numbering System		L-2
Dimmers		
Decorator Dimmers		
Scene Director Dimmers	120VAC, 60 Hz	L-3, L-4
Advanced Functionality Decorator Multilocation Dimmers	120VAC, 60 Hz	L-5
Advanced Functionality Decorator Dimmers	120VAC, 60 Hz	L-6
TradeMaster® Decorator Slide Dimmers	120VAC, 60 Hz	L-7
Decorator Slide Dimmers	120 & 277VAC, 60 Hz	L-8, L-9
TradeMaster® Short Slide Dimmers	120VAC, 60 Hz	L-10
Toggle Dimmers		
Advanced Functionality Toggle Dimmers	120VAC, 60 Hz	L-11
TradeMaster® Toggle Dimmers	120VAC, 60 Hz	L-12
Rotary Dimmers		
Incandescent, Low Voltage & Fluorescent Rotary Dimmers	120VAC, 60 Hz	L-13, L-14
Fan Speed Controls		
Decorator Fan Speed Controls		
Scene Director & Advanced Functionality Fan Speed Controls	120VAC, 60 Hz	L-15
TradeMaster® Decorator Slide Fan Speed Controls	120VAC, 60 Hz	L-16
Decorator Slide Fan Speed Controls	120VAC, 60 Hz	L-17
TradeMaster® Short Slide Fan Speed Controls	120VAC, 60 Hz	L-18
TradeMaster® Toggle Fan Speed Controls	120VAC, 60 Hz	L-18
Rotary Fan Speed Controls	120VAC, 60 Hz	L-19, L-20
Wall Box Timers		
Rotary Wall Box Timers	125, 125-T, 250 & 277VAC, 60 Hz	L-21
Toggle Wall Box Timers	500W, 1/3 HP, 120VAC, 60 Hz	L-22



TradeMaster® & Advanced Functionality Dimmers & Fan Speed Controls use an easy-to-understand catalog numbering system:

TLV 600 - *

Control Type

- D = Decorator
- DS = Decorator Slide
- SC = Scene Controller
- SS = Short Slide
- T = Toggle

Load Type

- Blank = Incandescent
- FB = Fluorescent Ballast
- IR = Infrared Remote
- LV = Low-Voltage
- ELV = Electronic Low-Voltage
- MC = Master Controller
- DC = Dual Control Dimmer/
Speed Control
- DH = De-Hummer
Fan Speed Control
- SC = Fan Speed Control
- R = Remote

Load Size

- 300 = 300 Watt
- 600 = 600 Watt/VA
- 603 = 600 Watt/VA,
3-Way
- 1000 = 1000 Watt/VA
- 1003 = 1000 Watt/VA,
3-Way
- 3 = 3 Amps
- 5 = 5 Amps
- 15 = 1.5 Amps
- 16 = 1.6 Amps

Package

- Blank = Box
- V = VisionPak™

Color

- CL = Clear
- GRY = Gray
- I = Ivory
- LA = Light Almond
- LC = Lighted Clear
- W = White

Options

- E = Electronic Preset
- L = Lighted
- M = Multilocation
- P = Preset

Examples:

- D600-MLAV** = Decorator Dimmer, Incandescent, 600W, Multilocation, Light Almond, in a VisionPak
- DS600-LLA** = Decorator Slide Dimmer, Incandescent, 600W, Lighted, Light Almond, in a Box
- SSSC5-WV** = Short Slide, Fan Speed Control, 5 Amp, White, in a VisionPak



Many P&S Dimmers & Fan Speed Controls are available boxed or VisionPak™ clam-shell packaging for high-impact merchandising. Please see the Catalog Numbering System above or specific charts for ordering information.