



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## D600RWH 600W SP Rotary Push Dimmer White

Lutron

Catalog Number	D600RWH
Manufacturer	Lutron
Description	Rotary Dimmer With Rotate On/Off Knob, Incandescent/Halogen, Single-Pole, 120V/600W In White
Weight per unit	0.2500 (lbs/each)
Product Category	Lighting Dimmers

### Features

actuator	Rotary Knob
connection	Wire Leads
Material	Size 0.13 Inch W x 0.16 Inch H; Thickness 0.062 Inch; Flammability Rating UL 94 HB; Temperature Range -40 to 122 Deg F; ROHS Compliant
Poles	1 PH
Voltage Rating	ELBOW FITTING, 316 STAINLESS STEEL MATERIAL; 1/2 INCH SIZE A; 1/2 INCH SIZE B; .5 SIZE A - DECIMAL; .5 SIZE B - DECIMAL; 1/2 SIZE A - FRACTIONAL; 1/2 SIZE B - FRACTIONAL; NUCLEAR, PHARMACEUTICAL INDUSTRY CHEMICAL, PETROCHEMICAL APPLICATION; CAST PROCESS
Wattage	94414

### Dimensions and Weight

Size	4.69 in (119 mm) x 2.94 in (75 mm)
------	------------------------------------

### Descriptions

Description	600W SP ROTARY PUSH DIMMER WHITE
extra long description	LUT D-600R-WH 600W INC ROTARY DIMME
Long Description	Rotary Dimmer with Rotate On/Off Knob, Incandescent/Halogen, Single-pole, 120V/600W in white
Product Type	600W Inc Rotary Dimmer WH
Special Features	Push on/off knob

### Manufacturer Information

Brand	Lutron
GTIN	00027557670036
Manufacturers Part Number	D-600R-WH
sub brand	Skylark
UPC	027557670036

### Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Incandescent/halogen dimmer



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status Inactive

## Packaging

Carton 1

Package 48

Weight Per each 0.25

## Uses, Certifications, and Standards

Application Lighting Control

Enclosure Plastic

environmental conditions Relative humidity less than 90 percentnon-condensing. Indoor use only

Frequency Rating 50-60 Hz

Mounting WALLBOX

Operating Temperature 0-40°C

standard UL, CSA