



Powering Business Worldwide

pe.eaton.com

Decorator Dimmer

DAL06P-C2

UPC:032664731075

Dimensions:

- **Height:** 5.9 IN
- **Length:** 2.1 IN
- **Width:** 3.8 IN

Weight: .28 LB

Warranties: No Data

Specifications:

- **Special Features:** Preset feature
- **Type:** Dimmer
- **Allowable Wire Size:** #14 - 12 AWG
- **Voltage Rating:** 120V
- **Wiring Method:** Back and side
- **Actuator:** Slide
- **Connection_Type:** Screw terminals
- **Color:** Light almond, white, ivory
- **Design Type:** Incandescent, halogen, magnetic low-voltage
- **Environmental Conditions:** Indoor
- **Frequency Rating:** 60 Hz
- **Load Type:** LED, CFL, incandescent, halogen, FLR, MLV, ELV
- **Switch Type:** Single-pole, three-way multi-location
- **Material:** Polycarbonate
- **Wattage:** 600W

Supporting documents: No Data

Certifications:

- NOM
- cULus Listed

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Decorator Dimmer

DAL06P-C2

UPC:032664731075

Dimensions:

- **Height:** 5.9 IN
- **Length:** 2.1 IN
- **Width:** 3.8 IN

Weight: .28 LB

Warranties: No Data

Specifications:

- **Special Features:** Preset feature
- **Type:** Dimmer
- **Allowable Wire Size:** #14 - 12 AWG
- **Voltage Rating:** 120V
- **Wiring Method:** Back and side
- **Actuator:** Slide
- **Connection_Type:** Screw terminals
- **Color:** Light almond, white, ivory
- **Design Type:** Incandescent, halogen, magnetic low-voltage
- **Environmental Conditions:** Indoor
- **Frequency Rating:** 60 Hz
- **Load Type:** LED, CFL, incandescent, halogen, FLR, MLV, ELV
- **Switch Type:** Single-pole, three-way multi-location
- **Material:** Polycarbonate
- **Wattage:** 600W

Supporting documents: No Data

Certifications:

- NOM
- cULus Listed

Product compliance: No Data



