



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Decorator Dimmer

**DAL06P-C2**

**UPC:**032664731075

### Dimensions:

- **Height:** 5.9 IN
- **Length:** 2.1 IN
- **Width:** 3.8 IN

**Weight:**.28 LB

**Warranties:** No Data

### Specifications:

- **Special Features:** Preset feature
- **Type:** Dimmer
- **Allowable Wire Size:** #14 - 12 AWG
- **Voltage Rating:** 120V
- **Wiring Method:** Back and side
- **Actuator:** Slide
- **Connection\_Type:** Screw terminals
- **Color:** Light almond, white, ivory
- **Design Type:** Incandescent, halogen, magnetic low-voltage
- **Environmental Conditions:** Indoor
- **Frequency Rating:** 60 Hz
- **Load Type:** LED, CFL, incandescent, halogen, FLR, MLV, ELV
- **Switch Type:** Single-pole, three-way multi-location
- **Material:** Polycarbonate
- **Wattage:** 600W

**Supporting documents:** No Data

### Certifications:

- NOM
- cULus Listed

**Product compliance:** No Data







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Decorator Dimmer

DAL06P-C2

UPC:032664731075

### Dimensions:

- **Height:** 5.9 IN
- **Length:** 2.1 IN
- **Width:** 3.8 IN

**Weight:** .28 LB

**Warranties:** No Data

### Specifications:

- **Special Features:** Preset feature
- **Type:** Dimmer
- **Allowable Wire Size:** #14 - 12 AWG
- **Voltage Rating:** 120V
- **Wiring Method:** Back and side
- **Actuator:** Slide
- **Connection\_Type:** Screw terminals
- **Color:** Light almond, white, ivory
- **Design Type:** Incandescent, halogen, magnetic low-voltage
- **Environmental Conditions:** Indoor
- **Frequency Rating:** 60 Hz
- **Load Type:** LED, CFL, incandescent, halogen, FLR, MLV, ELV
- **Switch Type:** Single-pole, three-way multi-location
- **Material:** Polycarbonate
- **Wattage:** 600W

**Supporting documents:** No Data

### Certifications:

- NOM
- cULus Listed

**Product compliance:** No Data



