# Eaton DG221NGB

# Catalog Number: DG221NGB

Eaton General duty cartridge fuse safety switch, 30 A, NEMA 1, Painted steel, Class H fuses, Fusible with neutral, Two-pole, Threewire, Category: general duty safety switch, 240 V

### General specifications



Catalog Number

Eaton general duty cartridge fuse safety DG221NGB

switch

UPC

782113120171

Product Length/Depth

**Product Height** 

6.89 in

10.23 in

**Product Width** 

**Product Weight** 

6.1 in

5.5 lb

Warranty

Compliances

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier

from the date of installation of the

Certifications Product or eighteen (18) months from the

date of shipment of the Product,

**UL Listed** 

whichever occurs first.

**Catalog Notes** 

Maximum hp ratings apply only when dual element fuses are used. 3-Phase hp rating shown is a grounded B phase

rating, UL listed.





## **Physical Attributes**

**Enclosure** 

NEMA 1

**Enclosure material** 

Painted steel

Fuse configuration

Fusible with neutral

**Number Of Poles** 

Two-pole

Number of wires

3

Type

General duty, cartridge fused

#### Performance Ratings

Amperage Rating

30A

Fuse class provision

Class H fuses

Voltage rating

240V

#### Miscellaneous

#### **Product Category**

General duty safety switch

#### Resources

#### Catalogs

Eaton's Volume 2—Commercial Distribution

Multimedia

Double Up on Safety

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - DG221NGB



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.









Eaton.com/socialmedia