# Eaton DG221UGB

# Catalog Number: DG221UGB

Eaton General duty non-fusible safety switch, single-throw, 30 A, NEMA 1, Indoor, Painted steel, Two-pole, Two-wire, 240 V

## General specifications



Catalog Number

Eaton general duty non-fusible safety

DG221UGB

switch

**UPC** 

782113120102

**Product Height** 

Product Length/Depth

6.88 in 10.69 in

**Product Width Product Weight** 

6.38 in 6 lb

Compliances Warranty

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier

from the date of installation of the

Certifications Product or eighteen (18) months from the

date of shipment of the Product,

**UL** Listed

whichever occurs first.

**Catalog Notes** 

WARNING! Switch is not approved for service entrance unless a neutral kit is

installed.





### default Taxonomy Attribute Label

Type

Non-fusible, single-throw

**Amperage Rating** 

30A

**Number Of Poles** 

Two-pole

**Product Category** 

General duty safety switch

Voltage rating

240V

Enclosure

NEMA 1

**Enclosure material** 

Painted steel

Fuse configuration

Non-fusible

Number of wires

2

#### Resources

#### Catalogs

Eaton's Volume 2—Commercial Distribution

Multimedia

Double Up on Safety

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - DG221UGB

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia