

# Eaton DG222NGB

Catalog Number: DG222NGB

Eaton General duty cartridge fuse safety switch, 60 A, NEMA 1, Painted steel, Class H fuses, Fusible with neutral, Two-pole, Three-wire, Category: general duty safety switch, 240 V



## General specifications

### Product Name

Eaton general duty cartridge fuse safety switch

### Catalog Number

DG222NGB

### UPC

782113144214

### Product Length/Depth

7.38 in

### Product Height

14.19 in

### Product Width

8.69 in

### Product Weight

10 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

### Certifications

UL Listed

### Catalog Notes

Maximum hp ratings apply only when dual element fuses are used. 3-Phase hp rating shown is a grounded B phase rating, UL listed.

## Physical Attributes

### Enclosure

NEMA 1

### Enclosure material

Painted steel

### Fuse configuration

Fusible with neutral

### Number Of Poles

Two-pole

### Number of wires

3

### Type

General duty, cartridge fused

## Performance Ratings

### Amperage Rating

60A

### Fuse class provision

Class H fuses

### Voltage rating

240V

## Miscellaneous

### Product Category

General duty safety switch

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

### Specifications and datasheets

[Eaton Specification Sheet - DG222NGB](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)