

# Eaton DG222UGB

Catalog Number: DG222UGB

Eaton General duty non-fusible safety switch, single-throw, 60 A, NEMA 1, Indoor, Painted steel, Two-pole, Two-wire, 240 V



Photo is representative

## General specifications

### Product Name

Eaton general duty non-fusible safety switch

### Catalog Number

DG222UGB

### UPC

782114731130

### Product Length/Depth

7.38 in

### Product Height

14.19 in

### Product Width

8.69 in

### Product Weight

9 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

### Certifications

UL Listed

### Catalog Notes

WARNING! Switch is not approved for service entrance unless a neutral kit is installed.

## defaultTaxonomyAttributeLabel

### Type

Non-fusible, single-throw

### Amperage Rating

60A

### Number Of Poles

Two-pole

### Product Category

General duty safety switch

### Voltage rating

240V

### Enclosure

NEMA 1

### Enclosure material

Painted steel

### Fuse configuration

Non-fusible

### Number of wires

2

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

### Specifications and datasheets

[Eaton Specification Sheet - DG222UGB](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)