

Eaton DG324URK

Catalog Number: DG324URK

Eaton General duty non-fusible safety switch, single-throw, 200 A, NEMA 3R, Rainproof, Painted galvanized steel, Three-pole, Three-wire, 240 V



General specifications

Product Name	Catalog Number
Eaton general duty non-fusible safety switch	DG324URK
	UPC
	782113213576

Product Length/Depth	Product Height
11.25 in	25.5 in

Product Width	Product Weight
16 in	55 lb

Warranty	Compliances
-----------------	--------------------

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications
UL Listed

Catalog Notes

WARNING! Switch is not approved for service entrance unless a neutral kit is installed.

Type

Non-fusible, single-throw

Amperage Rating

200A

Number Of Poles

Three-pole

Product Category

General duty safety switch

Voltage rating

240V

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Number of wires

3

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DG324URK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia