

Eaton DH222NRK

Catalog Number: DH222NRK

Eaton Heavy duty single-throw fused safety switch, 60 A, NEMA 3R, Painted galvanized steel, Neutral, Two-pole, Three-wire, 240 V, Max Hp: 3, 7.5 hp/10, 15 hp/10 hp (1,3PH @ Std fuse/time delay/250 Vdc), #14-#2 Cu/Al



General specifications

Product Name	Catalog Number
Eaton heavy duty fusible safety switch	DH222NRK
UPC	Product Length/Depth
782113205793	16.5 in
Product Height	Product Width
8.31 in	9.12 in
Product Weight	Warranty
19 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed CSA Certified	3-Phase hp ratings shown are grounded B phase ratings; UL listed

Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible with neutral

Number Of Poles

Two-pole

Number of wires

3

Type

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating

60A

HP rating - max

3, 7.5 hp/10, 15 hp/10 hp (1,3PH @ Std fuse/time delay/250 Vdc)

NEMA rating

NEMA 3R

Voltage rating

240V

Miscellaneous

Product Category

Heavy Duty, Fusible with neutral

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - DH222NRK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)