

# Eaton DH324NGK

Catalog Number: DH324NGK

Eaton Heavy duty single-throw fused safety switch, 200 A, NEMA 1, Painted steel, Class H, Neutral, Three-pole, Four-wire, 240 V, Max Hp: 15, 25/ 15, 60/ 40 hp (1,3PH @Std/TD/250 Vdc), #6-250 kcmil Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy duty fusible safety switch	DH324NGK
<b>UPC</b>	<b>Product Length/Depth</b>
782113206684	30 in
<b>Product Height</b>	<b>Product Width</b>
9.5 in	18 in
<b>Product Weight</b>	<b>Warranty</b>
40 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Compliances</b>	<b>Certifications</b>
NEC 230.62 (C) Compliant Barrier	UL Listed

## Physical Attributes

### Enclosure

NEMA 1

### Enclosure material

Painted steel

### Fuse class provision

Class H

### Fuse configuration

Fusible with neutral

### Number Of Poles

Three-pole

### Number of wires

4

### Type

Heavy duty fusible safety switch

### Wire size

#6 AWG-250 kcmil Cu/Al

## Performance Ratings

### Amperage Rating

200A

### HP rating - max

15, 25/ 15, 60/ 40 hp (1,3PH @Std/TD/250 Vdc)

### NEMA rating

NEMA 1

### Voltage rating

240V

## Miscellaneous

### Product Category

Heavy Duty, Fusible with neutral

## Resources

### Catalogs

[Switching devices catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - DH324NGK](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)