

Eaton DH363FGK

Catalog Number: DH363FGK

Eaton Custom single-throw fused safety switch, 100 A, NEMA 1, Painted steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 30, 40/ 60, 75 hp (1/3PH @480, 600 V), #14-#1/0 Cu/Al



Photo is representative

General specifications

Product Name	Catalog Number
Eaton custom single-throw fused safety switch	DH363FGK
	UPC
	782113206417
Product Length/Depth	Product Height
23.3 in	8.5 in
Product Width	Product Weight
13 in	21.7 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Suitable for service entrance use with a Neutral Kit installed

defaultTaxonomyAttributeLabel

Type

Heavy duty fusible safety switch

Amperage Rating

100A

Number Of Poles

Three-pole

Product Category

Heavy Duty, Fusible without neutral

Voltage rating

600 V

HP rating - max

30, 40/ 60, 75 hp (1/3PH @480, 600 V)

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

Number of wires

3

Resources

Brochures

[Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - DH363FGK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)