

Eaton DH363URK

Catalog Number: DH363URK

Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 100 A, NEMA 3R, Painted galvanized steel, Non-Fusible, Three-pole, Three-wire, 20 at 240 Vac TD 1 Ph, 40 at 480 Vac TD 1 Ph, 50 at 600 Vac TD 1 Ph, 40 at 240 Vac TD 3 Ph



General specifications

Product Name

Eaton heavy duty non-fusible safety switch

Catalog Number

DH363URK

UPC

782113206479

Product Length/Depth

9.89 in

Product Height

21.68 in

Product Width

11.84 in

Product Weight

22 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

Suitable for service entrance use with a neutral or ground lug kit installed

Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Number Of Poles

Three-pole

Number of wires

3

Type

Single-throw

Performance Ratings

Amperage Rating

100A

HP rating - max

20 at 240 Vac TD 1 Ph, 40 at 480 Vac TD 1 Ph, 50 at 600 Vac TD 1 Ph, 40 at 240 Vac TD 3 Ph, 75 at 480 Vac TD 3 Ph, 100 at 600 Vac TD 3 Ph, 20 at 250 Vdc

NEMA rating

NEMA 3R

Voltage rating

600 V

Miscellaneous

Product Category

Heavy Duty, Non-Fusible

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - DH363URK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)