

Eaton DH364FGK

Catalog Number: DH364FGK

Eaton Custom single-throw fused safety switch, 200 A, NEMA 1, Painted steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 50, 50/ 125, 150 hp (1/3PH @480, 600 V), #6-250 kcmil Cu/Al



General specifications

Product Name	Catalog Number
Eaton custom single-throw fused safety switch	DH364FGK
	UPC
	782113206783

Product Length/Depth	Product Height
30 in	9.5 in

Product Width	Product Weight
18 in	48 lb

Warranty	Certifications
-----------------	-----------------------

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Suitable for service entrance use with a Neutral Kit installed

defaultTaxonomyAttributeLabel

Type

Heavy duty fusible safety switch

Amperage Rating

200A

Number Of Poles

Three-pole

Product Category

Heavy Duty, Fusible without neutral

Voltage rating

600 V

HP rating - max

50, 50/ 125, 150 hp (1/3PH @480, 600 V)

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

Number of wires

3

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - DH364FGK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)