

# Eaton DH366FRK

Catalog Number: DH366FRK

Eaton Enhanced visible blade single-throw safety switch, 600 A, NEMA 3R, Painted galvanized steel, Class H, Three-pole, Three-wire, 600 V, Max Hp: 200, 400, 500 hp (3PH @240,480,600 V), (1)#2-(1)600 kcmil; and (1)#1/0-(1)750 kcmil Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy duty fusible safety switch	DH366FRK
<b>UPC</b>	<b>Product Length/Depth</b>
782113207568	58 in
<b>Product Height</b>	<b>Product Width</b>
12 in	27.5 in
<b>Product Weight</b>	<b>Warranty</b>
160 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed	Suitable for service entrance use with a Neutral Kit installed

## Physical Attributes

### Enclosure

NEMA 3R

### Enclosure material

Painted galvanized steel

### Fuse class provision

Class H

### Fuse configuration

Fusible without neutral

### Number Of Poles

Three-pole

### Number of wires

3

### Type

Heavy duty fusible safety switch

## Performance Ratings

### Amperage Rating

600A

### HP rating - max

200, 400, 500 hp (3PH @240,480,600 V)

### NEMA rating

NEMA 3R

### Voltage rating

600 V

## Miscellaneous

### Product Category

Heavy Duty, Fusible without neutral

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - DH366FRK](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)