

Specifications



Eaton DI06P-W

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Wht, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 600W 662386

General specifications

PRODUCT NAME	Eaton decorator dimmer
CATALOG NUMBER	DI06P-W
UPC	032664662386
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	4.25 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	NOM cULus Listed

Product specifications

FREQUENCY RATING	60 Hz
SPECIAL FEATURES	Preset
TYPE	Dimmer
VOLTAGE RATING	120 V
POWER CONSUMPTION	600 W
WIRING METHOD	Back a
ENVIRONMENTAL CONDITIONS	Indoor
SWITCH TYPE	Single three-
LOAD TYPE	INC MLV HAL
HOUSING	Polycarb
TORQUE RATING	14 lbf
MATERIAL	Polycarb
ACTUATOR	Slide
COLOR	White
CONNECTION TYPE	Wire l



Powering Business Worldwide