

Eaton DI10P-V

Catalog Number: DI10P-V

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Ivory, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 1000W 662430



General specifications

Product Name	Catalog Number
Eaton decorator dimmer	DI10P-V
UPC	Product Length/Depth
032664662430	2.063 in
Product Height	Product Width
4.375 in	3.125 in
Product Weight	Certifications
0.001 lb	cULus Listed NOM

Product specifications

Special features

Preset feature

Switch type

Single-pole, three-way

Load type

MLV

INC

HAL

Color

Ivory

Wiring method

Back and side

Material

Polycarbonate

Housing

Polycarbonate

Type

Dimmer

Power consumption

1000 W

Environmental conditions

Indoor

Frequency rating

60 Hz

Connection type

Wire lead

Voltage rating

120 V

Torque rating

14 lbf-inch

Actuator

Slide

Resources

Brochures

[Lighting controls line card brochure](#)

Installation videos

[How to install Eaton's universal slide dimmers](#)

Specifications and datasheets

[Eaton Specification Sheet - DI10P-V](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)