



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DITD12V20W 20W 12V Omnidrive Dimmable

Diode Led

Catalog Number	DITD12V20W
Manufacturer	Diode Led
Description	Recessed Gimbal Led Fixture, Dimmable, Led For Bulb Type, 1.1 In Height, 0.14 A Input Current Rating, 110 V Ac Input Voltage Rating, 5.5 In Length, +176°F;+80°C Maximum Operating Temperature, -40 °F Minimum Operating Temperature, 1.66 A Output Current Rating, 12 V DC Output Voltage Rating, 20 W Output Wattage, Smooth, Flicker-Free Dimming Special Features, Culus Listed, 3.8 Oz Weight, 1.8 In Width
Weight per unit	0.5000 (lbs/each)
Product Category	Led Emergency Drivers

Features

Category	Specialty Items
Safety Rating	UL mA

Material, Color, and Finish

Finish	WHITE GLOSS
Style	Transitional

Descriptions

Description	20W 12V OMNIDRIVE DIMMABLE
-------------	----------------------------

Manufacturer Information

Brand	Diode Led
GTIN	00848333002687
Manufacturers Part Number	DI-TD-12V-20W
UPC	848333002687

Taxonomies, Classifications, and Categories

Category Description	DIMMING BALLASTS
Type	Fixture Accents/Parts

Packaging

Carton	1
Weight Per each	0.5