


# NICOR<sup>®</sup> | LED


## 2" LED Downlight Series **DLR2 | DQR2 | DLG2**



Small lights. **Big impact.**

# DLR2

## 2" Recessed LED Downlight



Dimmable



Die Cast Aluminum



Optic Options



Lumen Output



Color Rendering Index

### TRIM OPTIONS

WHITE

NICKEL

OIL RUBBED BRONZE

BLACK




### TRIM OPTIONS

- Smooth
- Baffle



# DLR2

## 2" Recessed LED Downlight w/baffle



WHITE

NICKEL

OIL RUBBED BRONZE

BLACK

### TRIM OPTIONS



Dimmable



Die Cast Aluminum



Optic Options



Lumen Output



Color Rendering Index

**Construction**

- Cast aluminum trim routes heat away from electrical components
- NICOR 2" LED housing required for use of 2" LED Downlight Series

**Optical System**

- Optical lens diffusers eliminate "hot spots" and provide smooth, uniform light
- Beam spread options available: Standard Flood, Narrow Flood, and Spot

**Electrical**

- Utilizes high performing LEDs with greater than 90 CRI and an R9 greater than 50
- Dimmable to 10% with most standard triac dimmers
- Operating temperature rating of 0°F to 120°F (-18°C to 49°C)
- Lifetime rated for greater than 35,000 hours
- LM-79, LM-80 testing performed in accordance with IESNA standards
- 120V input to driver

**Finish**

- Exterior white powder coat finish
- Also available in Black, Oil-Rubbed Bronze and Nickel

**Installation**

- NICOR's 2" recessed housings required: Available in remodel, new construction, and IC/ Airtight new construction
- Quick and easy installation with a snap-in IDEAL connector and friction clip mounting system

**Warranty**

- 5-year limited system warranty standard

Product Information	DLR2	DQR2	DQR2-AA	DLG2
<b>LED Lifetime:</b>	35,000 hrs	35,000 hrs	35,000 hrs	35,000 hrs
<b>Input Voltage:</b> (input to driver located in 2" housing)	120V	120V	120V	120V
<b>Power Draw:</b>	9W	9W	9W	9W
<b>Delivered Lumens*:</b>	680 Lm	631 Lm	696 Lm	700 Lm
<b>System Efficacy*:</b>	78 Lm/W	71 Lm/W	81 Lm/W	82 Lm/W
<b>Correlated Color Temp:</b>	3000K	3000K	3000K	3000K
<b>Color Rendering Index:</b>	93 CRI	93 CRI	92 CRI	92 CRI

\* Performance data shown at 3000K  
For more information, visit [www.nicorlighting.com](http://www.nicorlighting.com)



DLG2 & DQR2-AA not Wet Location Rated

**ORDERING INFORMATION**

Example: DLR2-10-120-3K-WH-BF-NF

Series	Version	Housing Input Voltage	CCT's	Trim	Baffle	Optics
DLR2	10 (v 1.0)	120 (V)	2K (2700)	WH (white)	blank (no baffle)	blank (37" Standard Optic)
DQR2			3K (3000)	BK (black)*	BF (baffle)**	NF (30" Narrow Optic)
DQR2-AA			4K (4000)	NK (nickel)*		SP (20" Spot Optic)
DLG2				OB (oil-rubbed bronze)*		

\* only available as special order. Contact NICOR for more info.  
\*\* only available for DLR2 and DQR2.

**LED Housings**

**Remodel Housing**



**ORDERING INFORMATION**

Catalog Number	Description
12202R-LED	2" LED Remodel Housing


**New Construction Housing**



**ORDERING INFORMATION**

Catalog Number	Description
12201-LED	2" LED New Construction Housing

**New Construction IC Rated Housing**



**ORDERING INFORMATION**

Catalog Number	Description
12200A-LED	2" LED IC/AT New Construction Housing