



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

500 Rapides Drive
71457-0000, LA Natchitoches
Phone: 318-352-7414
Fax: 318-352-4100



DNF10250FIBL 10-12AWG Ylw Inslted FML DSCNCT *Panduit Corporation*

Catalog Number	DNF10250FIBL
Manufacturer	Panduit Corporation
Description	Panduit DNF10-250FIB-L Female Disconnect
Weight per unit	0.2700 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Nylon
Material	Brass
media	Yes
Voltage Rating	600
Wire Size	10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Descriptions

Description	10-12AWG YLW INSLTD FML DSCNCT
extra long description	PAN DNF10-250FIB-L Pan-Term® DNF10-
Long Description	Panduit DNF10-250FIB-L Female Disconnect
Product Type	Pan-Term® DNF10-250FIB-L Disconnect, Ylw, Nylon, 10-12 Awg,

Manufacturer Information

Brand	Panduit®
GTIN	00074983740529
Manufacturers Part Number	DNF10-250FIB-L
UPC	074983740529

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Disconnect

Availability

minimum qty	50
-------------	----

Packaging

Carton	50
Weight Per each	0.27



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

500 Rapides Drive
71457-0000, LA Natchitoches
Phone: 318-352-7414
Fax: 318-352-4100

Uses, Certifications, and Standards

Mounting	3/8
standard	UL 310, CSA 22.2 No.153
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)