



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DNFR14250BL 14-16AWG 90D Blue FML Discnct *Panduit Corporation*

|                  |   |
|------------------|---|
| Catalog Number   | DNFR14250BL                             |
| Manufacturer     | Panduit Corporation                     |
| Description      | Panduit DNFR14-250B-L Female Disconnect |
| Weight per unit  | 0.4050 (lbs/each)                       |
| Product Category | Small Terminals & Connectors            |

### Features

|                |              |
|----------------|--------------|
| connection     | Funnel Entry |
| insulation     | Nylon        |
| Material       | Brass        |
| media          | Yes          |
| Voltage Rating | 600          |
| Wire Size      | #14          |

### Material, Color, and Finish

|        |        |
|--------|--------|
| Color  | Blue   |
| Finish | Tinned |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 14-16AWG 90D BLUE FML DISCNCT                               |
| extra long description | PAN DNFR14-250B-L Pan-Term® DNFR14-                         |
| Long Description       | Panduit DNFR14-250B-L Female Disconnect                     |
| Product Type           | Pan-Term® DNFR14-250B-L Disconnect, 90°, Blue, Nylon, 14-16 |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | PANDUIT        |
| GTIN                      | 00074983124572 |
| Manufacturers Part Number | DNFR14-250B-L  |
| UPC                       | 074983124572   |

### Taxonomies, Classifications, and Categories

|      |            |
|------|------------|
| Type | Disconnect |
|------|------------|

### Availability

|             |    |
|-------------|----|
| minimum qty | 50 |
|-------------|----|

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 50    |
| Weight Per each | 0.405 |

### Uses, Certifications, and Standards

|                    |  |
|--------------------|--|
| Mounting           | 9/32   |
| standard           | UL 310, CSA 22.2 No.153                      |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |