



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2400 N Stallings Drive  
75964-0000, TX Nacogdoches  
Phone: 936-715-4010  
Fax: 936-715-4039



## **DR20WHITR Tamper Res, Deco Face, 20A 125V, WH** *Hubbell Wiring Devices*

Catalog Number	DR20WHITR
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Tamper-Resistant Duplex, Decorator/Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, White, Single Pack.
Weight per unit	0.0460 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### **Features**

amperage rating	20
connection	Back and Side Wired
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
pallet quantity	8000
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	2500
Wire Size	#12 to #10

### **Dimensions and Weight**

Size	3.28 in x 1.14 in x 1.29 in
------	-----------------------------

### **Descriptions**

Description	TAMP RES, DECO FACE, 20A 125V,WH
extra long description	HWDK DR20WHITR TAMP RES, DECO FACE,
Long Description	Straight Blade Devices, Receptacles, Tamper-Resistant Duplex, Decorator/Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, White, Single Pack.
Product Type	Tamp Res, Deco Face, 20A 125V, WH
Special Features	Tamper Resistant

### **Manufacturer Information**

Brand	Hubbell Wiring Devices
GTIN	00783585144443
Manufacturers Part Number	DR20WHITR
series	Commercial Specification Grade
UPC	783585144443



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2400 N Stallings Drive  
75964-0000, TX Nacogdoches  
Phone: 936-715-4010  
Fax: 936-715-4039

## Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Tamper-Resistant

## Packaging

Carton	1
Package	10
Weight Per each	0.046

## Uses, Certifications, and Standards

Application	Commercial Specification Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA, C22.2, No. 42;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186