



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DS441 DS441 Box Cover *Crouse-Hinds*

Catalog Number	DS441
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Flexstation DS Blank Cover, Feraloy Iron Alloy, Single-Gang, Single Hole Cover
Weight per unit	3.4 (lbs/each)
Product Category	Wall Plates & Covers

### Features

dimensions	5.3000 IN X 4.6000 IN X 6.8000 IN
Material	FERALOY IRON ALLOY
Shape	Rectangular

### Material, Color, and Finish

Color	Natural
Finish	Natural

### Dimensions and Weight

Size	5-7/8 In Length X 3-1/2 In Width X 2-11/18 In Depth
------	---

### Descriptions

Description	DS441 BOX COVER
extra long description	CRS-H DS441 EDS/EDSC/EFS/EFSC SIN/M
Features	Crouse-Hinds series FlexStation components are combined to provide a variety of control stations which are used in conjunction with magnetic starters or contactors for remote control of motors and other electrical apparatus. Used in petroleum refineries, chemical, petrochemical; grain processing and storage; heavy industrial applications where Class I, II, or III hazards are present.
Long Description	Eaton Crouse-Hinds series FlexStation DS blank cover, Feraloy iron alloy, Single-gang, Single hole cover
Product Type	Eds/Edsc/Efs/Efsc Sin/Multi GNG Dev Body
Special Features	Single Gang, NEMA 3R/7B/7C/7D/9E/9F/9G/12

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274147451
Manufacturers Part Number	DS441
UPC	782274147451

### Taxonomies, Classifications, and Categories

Category Description	FS BOXES AND COVERS
Type	BLANK COVER



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	3.35

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
standard	UL 1203