



Asbestos Free Duct Sealing Compound

1 LB Block – Peco Catalog# DS-1

5 LB Block – Peco Catalog# DS-5

Asbestos Free Sealer is gray, permanently soft, non-toxic compound, which will adhere to most clean surfaces. It will not adversely affect other plastic materials or corrode materials. It also has no adverse affect to human skin.

Primarily used by the building industry and specifically the electrical trade to seal around electrical boxes, flashings, and service mast entries, etc. It can be shaped by hand into any form and reused if necessary. There are countless other applications in the refrigeration, heating and cooling, plumbing, and metal fabrication fields. It may be painted immediately after application, and will not bleed through the dry paint.

- FDA Approved – Listed in CFR, Title 21, as being composed of ingredients acceptable for packaging and transporting food.
- U.S.D.A. Acceptable – Chemically acceptable to the U.S.D.A. for use in meat and poultry processing areas under Federal inspection.
- Dielectric Strength – Approximately 200 volts per mil (ASTM D149-64) or 10 KV.
- Chemical Resistance – Excellent resistance to water, alchols, mild acids and bases.
- Non-Corrosive – Will no corrode metals
- Non-Irritant – No irritation to eyes or skin as listed in CFR, Title 16.
- Paintable
- UL Classified R11374 – General Use Tapes
- Temperature Usage Range – 25 to 120 Degrees Fahrenheit
- Temperature Tolerance Range - -30 to 175 Degrees Fahrenheit