



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DV18250BCY 22-18 Vinyl Ins Female Disconnect Red *Panduit Corporation*

Catalog Number	DV18250BCY
Manufacturer	Panduit Corporation
Description	The Vibration Resistant Female Disconnect Is Made Of Brass and Is Tin-Plated. It Is Barrel Insulated In Red Vinyl Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 22-18 Awg (0.5-1.0 MM <sup>2</sup> ). It Is 0.81" (20.6 MM) Long and 0.29" (7.4 MM) Wide. The Disconnect Has A Funnel Entry Barrel Configuration and A Butted Seam Barrel. It Comes In Bottles Of 100.
Weight per unit	0.2300 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Funnel Entry
insulation	Vinyl
Material	Brass
Voltage Rating	600
Wire Size	#18

### Material, Color, and Finish

Color	Red
Finish	Tinned

### Descriptions

Description	22-18 VINYL INS FEMALE DISCONNECT RED
extra long description	PAN DV18-250B-CY Pan-Term® DV18-250
Long Description	The vibration resistant female disconnect is made of brass and is tin-plated. It is barrel insulated in red vinyl housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 22-18 AWG (0.5-1.0 mm <sup>2</sup> ). It is 0.81" (20.6 mm) long and 0.29" (7.4 mm) wide. The disconnect has a funnel entry barrel configuration and a butted seam barrel. It comes in bottles of 100.
Product Type	Pan-Term® DV18-250B-Cy Loose Piece Disconnect

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983685615
Manufacturers Part Number	DV18-250B-CY
UPC	074983685615



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Disconnect

## Availability

minimum qty	100
-------------	-----

## Packaging

Carton	100
Package	500
Weight Per each	0.23

## Uses, Certifications, and Standards

Mounting	1932-09-01
standard	CSA Certified LR31212, C22.2 No.153;UL 310 Listed, UL Listed 20H3 E78522
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)