



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DVCL153PHWH Diva 150W Led 3WAY White Clam

Lutron

Catalog Number	DVCL153PHWH
Manufacturer	Lutron
Description	Dimmable Bulb, Wallbox Switch, 120 V, 150 W;600 W, 60 HZ, Dimmable CFL/Led;Incandescent/Halogen Lamp, Wall Mount, 2.94 In Length, 2.75 In Width, 4.69 In Height, White, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.25 LB/Ea
Weight per unit	0.2700 (lbs/each)
Product Category	Lighting Dimmers

### Features

Connection Type	Wire Leads
insulation	Plastic
media	Yes
Poles	1
Voltage Rating	120
Wattage	600

### Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

### Descriptions

Description	DIVA 150W LED 3WAY WHITE CLAM
extra long description	LUT DVCL-153PH-WH DIVA CFL/LED CLAM
Long Description	Dimmable Bulb, Wallbox Switch, 120 V, 150 W;600 W, 60 HZ, Dimmable CFL/Led;Incandescent/Halogen Lamp, Wall Mount, 2.94 In Length, 2.75 In Width, 4.69 In Height, White, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.25 LB/Ea
Special Features	Controls 150 W dimmable LED/CFL (screw-base), 600 W incandescent, or halogen loads. Paddle turns on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs, as well as halogens and incandescents.

### Manufacturer Information

GTIN	00027557003322
UPC	027557003322

### Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer, 3-way/single-pole, clamshell packaging



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	3
Package	48
Weight Per each	0.27

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	WALLBOX
standard	UL, CSA, NOM