



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DVRP253PWH Diva 250W Led/Electronic Low Voltage 3WAY White

Lutron

Catalog Number	DVRP253PWH
Manufacturer	Lutron
Description	Diva Reverse-Phase Dimmer - Gloss Finish, CFL/Led (Screw-Based), Incandescent/Halogen, Electronic Low-Voltage, 3-Way/Single-Pole, 250W CFL/Led or 500W Inc/Hal/Elv In White
Weight per unit	0.2700 (lbs/each)
Product Category	Lighting Dimmers

### Features

actuator	Paddle Switch
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
Poles	1
Switch Type	Paddle Switch
Voltage Rating	120
Wattage	250/500

### Material, Color, and Finish

Color	White
-------	-------

### Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

### Descriptions

Description	DIVA 250W LED/ELECTRONIC LOW VOLTAGE 3WAY WHITE
extra long description	LUT DVRP-253P-WH DIVA 250W LED 500W
Long Description	Diva Reverse-phase Dimmer - Gloss Finish, CFL/LED (Screw-based), Incandescent/Halogen, Electronic Low-voltage, 3-way/single-pole, 250W CFL/LED or 500W inc/hal/ELV in white
Product Type	Diva 250W Led 500W Elv In White
Special Features	Controls 120 V/250 W LED/CFL, and 500 W Inc and ELV loads. Paddle turns on/off. Slide up to brighten, down to dim.

### Manufacturer Information

Brand	Lutron
GTIN	00784276221665
Manufacturers Part Number	DVRP-253P-WH
UPC	784276221665



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer, reverse-phase, 3-way/single-pole

## Packaging

Carton	1
Weight Per each	0.27

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, CSA, NOM