



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DVSTVNHEIV Diva Dimmer - Gloss Finis *Lutron*

Catalog Number	DVSTVNHEIV
Manufacturer	Lutron
Description	
Weight per unit	0.2600 (lbs/each)
Product Category	Lighting

Features

actuator	Paddle Switch
amperage rating	Tapswitch
Cable Size	32 to 104
connection	Wire Leads
insulation	Plastic
Lamp Type	Tapswitch
Material	METAL/PLASTIC
Mounting Type	Tapswitch
Poles	125
sensing range	SensorSwitch
terminals	Tapswitch
Voltage Rating	120 to 277
Wattage	2216

Material, Color, and Finish

Color	Ivory
-------	-------

Dimensions and Weight

Height	32 to 104
Size	4.69 in (119 mm) x 2.94 in (75 mm)

Descriptions

Description	DIVA DIMMER - GLOSS FINIS
extra long description	LUT DVSTV-NHE-IV OBS NOV 2022 DIVA
Product Type	Obs Nov 2022 Diva 0-10V Dimmer, Ivory
Special Features	Tapswitch

Manufacturer Information

Brand	Lutron
GTIN	00784276293891
Manufacturers Part Number	DVSTV-NHE-IV
sub brand	Diva
UPC	784276293891

Taxonomies, Classifications, and Categories

Type	Dimmer, 3-way/single-pole
------	---------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Manufacturer Status Inactive

Packaging

Carton 1

Weight Tapswitch

Weight Per each 0.26

Uses, Certifications, and Standards

Application Tapswitch

Enclosure Plastic

environmental conditions Indoor use only

Frequency Rating 60

Mounting WALLBOX

Operating Temperature 32 to 104 F (0 to 40 C)

standard UL, CSA