



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E101B 24HR 40A SPST Digital Clock With Supercap

*Nsi Industries*

Catalog Number	E101B
Manufacturer	Nsi Industries
Description	Digital Clock With Supercap, 24 H Time Setting Mode, SPST Contact Form, 24 H Time Setting, 120 to 277 V Ac, 40 A (No) @ 120 to 277 V Ac (General Purpose);30 A (No) @ 120 V Ac;20 A (No) @ 208 to 277 V Ac (Ballast);15 A (No) @ 120 V Ac (Tungsten);30 A @ 28 V DC (Resistive);40 A (No) @ 120 to 277 V Ac (Inductive), 20 On/Off Cycles, Plastic Enclosure Material, Screw Connection, -40 °F Operating Temperature, +149 °F Operating Temperature, 5.062 X 3.062 X 8.312 In Size, 2 LB
Weight per unit	2.0 (lbs/each)
Product Category	Electronic Time Switches

### Features

action	SPST
Base	Screw
Contact Rating	120-277 VAC
Phase	Single Phase
Poles	1
Timing Range	24 Hour

### Descriptions

Description	24HR 40A SPST DIGITAL CLOCK WITH SUPERCAP
extra long description	TORK E101B 24 Hr Digital Timer SPST

### Manufacturer Information

GTIN	00786261824011
UPC	786261824011

### Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	24 Hour Time Switch - 1 Or 2 Channel

### Packaging

Carton	1
Weight Per each	2



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Enclosure	NEMA 3R Plastic Indoor-Outdoor
environmental conditions	-40 to + 149 F
Frequency Rating	50-60 Hz
Mounting	Screw Mount
Operating Temperature	-40 to + 149 F
standard	UL917