



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E101B 24HR 40A SPST Digital Clock With Supercap

Nsi Industries

| | |
|------------------|---|
| Catalog Number | E101B |
| Manufacturer | Nsi Industries |
| Description | Digital Clock With Supercap, 24 H Time Setting Mode, SPST Contact Form, 24 H Time Setting, 120 to 277 V Ac, 40 A (No) @ 120 to 277 V Ac (General Purpose);30 A (No) @ 120 V Ac;20 A (No) @ 208 to 277 V Ac (Ballast);15 A (No) @ 120 V Ac (Tungsten);30 A @ 28 V DC (Resistive);40 A (No) @ 120 to 277 V Ac (Inductive), 20 On/Off Cycles, Plastic Enclosure Material, Screw Connection, -40 °F Operating Temperature, +149 °F Operating Temperature, 5.062 X 3.062 X 8.312 In Size, 2 LB |
| Weight per unit | 2.0 (lbs/each) |
| Product Category | Electronic Time Switches |

Features

| | |
|----------------|--------------|
| action | SPST |
| Base | Screw |
| Contact Rating | 120-277 VAC |
| Phase | Single Phase |
| Poles | 1 |
| Timing Range | 24 Hour |

Descriptions

| | |
|------------------------|---|
| Description | 24HR 40A SPST DIGITAL CLOCK WITH SUPERCAP |
| extra long description | TORK E101B 24 Hr Digital Timer SPST |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00786261824011 |
| UPC | 786261824011 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------------------|
| Category Description | TIME CLOCKS |
| Type | 24 Hour Time Switch - 1 Or 2 Channel |

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Weight Per each | 2 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--------------------------------|
| Enclosure | NEMA 3R Plastic Indoor-Outdoor |
| environmental conditions | -40 to + 149 F |
| Frequency Rating | 50-60 Hz |
| Mounting | Screw Mount |
| Operating Temperature | -40 to + 149 F |
| standard | UL917 |