

Eaton E1049-1814ST-BL

Catalog Number: E1049-1814ST-BL

Eaton Crouse-Hinds series Roughneck E1049 receptacle assembly, Up to 1135A continuous, 313-777 kcmil, Blue, Male, Short throw, Rubber, Double hole bus bar, 1000 Vac/dc

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Roughneck E1049 receptacle assembly	E1049-1814ST-BL
	UPC
	662275919632
Product Length/Depth	Product Height
10.25 in	4.25 in
Product Width	Product Weight
4.25 in	9.5 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3

Product specifications

Cable size

313-777 kcmil

Amperage Rating

Up to 1135A Continuous

Voltage rating

1000 Vac/dc

Gender

Male

Color

Blue

Latch type

Short throw

Type

Double hole bus bar

Material

Rubber

Resources

Brochures

[Roughneck Single Pole High-amperage Plugs and Connectors brochure](#)

Catalogs

[Roughneck Single Pole High Amperage Plugs and Connectors catalog page](#)

Installation instructions

[IF 1777 - Roughneck E1049 Series Connectors](#)

[IF 1778 - Roughneck E1049 Series Connectors and Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - E1049-1814ST-BL](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)