

Eaton E30AG

Catalog Number: E30AG

Eaton E30 pushbutton operator, 2C BTN MA W/RBAR MECH INLK, E30, 30.5 mm, Square Multifunction, NEMA 3, 3R, 4, 12, 13, Non-illuminated, Maintained (top and bottom), Two button, long (OFF) release bar,

Photo is representative



General specifications

Product Name	Catalog Number
Eaton E30 pushbutton operator	E30AG
UPC	Product Length/Depth
782113214085	1.9 in
Product Height	Product Width
2.3 in	2 in
Product Weight	Warranty
0.35 lb	1 year
Certifications	Catalog Notes
UL Listed CSA Certified	Operator is supplied as standard with red extended bar marked (OFF). Includes Mechanical Interlock.

defaultTaxonomyAttributeLabel

Type

30.5 mm, Square Multifunction

Actuator

Two button, long (OFF) release bar

Operating mode

Bottom: maintained

Top: maintained

Illumination

Non-illuminated

Series

E30

Rating

NEMA 13

NEMA 3

NEMA 4

NEMA 12

NEMA 3R

Resources

Brochures

[Non-Illuminated Rotary Cam Type Selector Switches](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E30AG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)