

Eaton E34VFBL1

Catalog Number: E34VFBL1

Eaton E34 pushbutton, E34, 30.5 mm, Corrosion Resistant, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Lever, Black actuator



General specifications

Product Name	Catalog Number
Eaton E34 pushbutton	E34VFBL1
UPC	Product Length/Depth
782113722825	1.9 in
Product Height	Product Width
2.1 in	1.8 in
Product Weight	Warranty
0.2 lb	1 year
Compliances	Certifications
FDA 3-A	CSA Certified
CE Marked	UL Listed

Catalog Notes

Use NEMA 4X 10250T operators where exposed to ultraviolet light

Type

30.5 mm, Corrosion Resistant

Actuator color

Black

Cam code

Cam 1

Actuator

Lever

Illumination

Non-illuminated

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Series

E34

Number of positions

2

Throw type

60 °

Brochures

10250T and E34 Class I Division 2

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Cam selection for pushbutton selectors

Eaton Specification Sheet - E34VFBL1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia