

Eaton E50DM1

Catalog Number: E50DM1

Eaton E50 NEMA heavy duty plug-in limit switch, Side rotary, maintained 2 position, Die cast zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, 14° to 201°F (-10° to 94°C), E50 Heavy Duty Plug In



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit E50DM1 switch	UPC 782113290584
Product Length/Depth 1.05 in	Product Height 2.46 in
Product Width 1.54 in	Product Weight 0.11 lb
Warranty 1 year	Compliances RoHS Compliant
Certifications UL Recognized CSA Certified	

defaultTaxonomyAttributeLabel

Enclosure material

Die cast zinc

Actuator

Side rotary, maintained 2 position

Series

E50 heavy duty plug in

Operating temperature - max

201 °F

Operating temperature - min

14 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50DM1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)