



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E50SAN E50 Switch Body With 120VAC Neon Indicating Light

Eaton Corp

Catalog Number	E50SAN
Manufacturer	Eaton Corp
Description	Limit Switch Body, E50 Heavy Duty Plug In Series, 1NO-1NC Contact Configuration, 10 A (Maximum Ac);1 A (Maximum DC), 12 V Ac;125 V DC, 1 Pole, Die Cast Zinc (Enclosure) Housing Material, -40 to +250 °F, 3.14 In Overall Length, 1.54 In Overall Width, 1.73 In Overall Depth, 0.4100 LB/Ea
Weight per unit	0.4100 (lbs/each)
Product Category	Limit Switch Bodies

Features

Contact Rating	10A at 12 Vac, 1A at 125 Vdc
dimensions	3.1400 IN X 1.5400 IN X 1.7300 IN
Poles	Single-pole

Descriptions

Description	E50 SWITCH BODY WITH 120VAC NEON INDICATING LIGHT
extra long description	ETN E50SAN E50 LS SWITCH BODY,NONC,

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113290690
UPC	782113290690

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch

Packaging

Carton	1
Weight Per each	0.41

Uses, Certifications, and Standards

Application	Water and Wastewater Systems - Water and Wastewater Systems - OtherStationary Mach Equip In Factory - Machine Tools: CuttingStationary Mach Equip In Factory - Machine Tools: FormingInd Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL Recognized,CSA Certified,UL Listed,RoHS Compliant,CE Marked