

Eaton E51SCN

Catalog Number: E51SCN

Eaton E51 NEMA limit switch inductive proximity sensor, Inductive Proximity Switch body, E51 Modular, Assembly, Output ON (1 LED per output), 1.0 A solid state output, L1 switched, 120V



General specifications

Product Name	Catalog Number
Eaton E51 NEMA limit switch inductive proximity sensor	E51SCN
	UPC
	782113213224
Product Length/Depth	Product Height
3.14 in	1.93 in
Product Width	Product Weight
1.54 in	0.31 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified

defaultTaxonomyAttributeLabel

Type

Assembly

Contact Rating

1.0A solid state output

Enclosure material

Die cast zinc

Contact configuration

L1 switched

Series

E51 modular

Environmental rating

NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P,
NEMA 12, NEMA 13, IP67

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Maximum AC current

1 A

Input voltage

120 V

LED indicator

Output ON (1 LED per output)

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E51SCN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)