

Eaton E57-18LE12-AA

Catalog Number: E57-18LE12-AA

Premium+ Inductive Proximity Sensor, E57, Straight, Shielded, 360° viewable LED, Dual key micro, 250 mA at 250V, 3 pin, <3% sensing range, 2-wire AC, NO, 20-132V



General specifications

Product Name	Catalog Number
Eaton E57 inductive proximity sensor	E57-18LE12-AA
UPC	Product Length/Depth
782113933375	2.72 in
Product Height	Product Width
0.71 in	0.71 in
Product Weight	Warranty
0.1 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified

defaultTaxonomyAttributeLabel

Type

Premium+ Inductive Proximity Sensor

Contact Rating

250 mA at 250V

Actuator function

Shielded

Accuracy

< 3% sensing range

Enclosure material

303 stainless steel

Connection

Dual key micro

Contact configuration

2-wire AC, NO

Series

E57

Environmental rating

NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13,
IP67, IP69K

Number of pins

3

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Maximum AC current

250 mA

Input voltage

20-132 V

LED indicator

360 ° viewable LED

Resources

Catalogs

[Product Range Catalog Sensors – products, basic information, applications](#)

[Eaton's Volume 8—Sensing Solutions](#)

Multimedia

[We make what matters](#)

Specifications and datasheets

[Eaton Specification Sheet - E57-18LE12-AA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)