



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E5730GU15GDB 30MM Diameter- 3W DC- Micro Conn PNP Unshielded 36 Eaton Corp

Catalog Number	E5730GU15GDB
Manufacturer	Eaton Corp
Description	Eaton Inductive Global Proximity Sensor, E57, 15 MM Range, Straight, 30 MM, Unshielded, Output On, M12, 100 Ma At 10-30 VDC, 4 Pin, <1.0% Sensing Range, PNP Open Collector, No, 10-30 VDC
Weight per unit	0.5000 (lbs/each)
Product Category	Inductive Proximity Sensor

Features

Accuracy	< 1.0% sensing range
connection	M12
dimensions	2.9500 IN X 1.1800 IN X 1.1800 IN
media	Yes

Descriptions

Description	30MM DIAMETER- 3W DC- MICRO CONN PNP UNSHIELDED 36
extra long description	ETN E57-30GU15-GDB Eaton E57 induct
Features	E57G general purpose sensors are a cost-effective solution that is optimised to include only those functions that are necessary for basic, reliable sensing without lacking the performance or features you expect in an Eaton product. These sensors include various diameter options designed to fit a variety of applications.
Long Description	Eaton Inductive Global Proximity Sensor, E57, 15 mm range, Straight, 30 mm, Unshielded, Output ON, M12, 100 mA at 10-30 Vdc, 4 pin, <1.0% sensing range, PNP open collector, NO, 10-30 Vdc
Product Type	Eaton E57 Inductive Proximity Sensor

Manufacturer Information

Brand	Eaton
GTIN	00782114665176
Manufacturers Part Number	E57-30GU15-GDB
UPC	782114665176

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Inductive Proximity Sensor

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.5

Uses, Certifications, and Standards

Application	Stationary Mach Equip In Factory - Other Stationary Machinery and Equipment - In Factory
environmental conditions	IP67, IP69K
standard	UL Listed, CSA Certified, CE Marked