

Specifications

Eaton E57LAL12T110



Premium+ Inductive Proximity Sensor, E57, 2 mm range, Straight, 12 mm, Shielded, 360° viewable LED, 6.6 ft, 500 mA at 6-30 Vdc, <1% sensing range, PVC, NO NPN open collector, 6-48 Vdc



General specifications

PRODUCT NAME	Eaton E57 inductive proximity sensor
CATALOG NUMBER	E57LAL12T110
UPC	782113742960
PRODUCT LENGTH/DEPTH	2.46 in
PRODUCT HEIGHT	0.47 in
PRODUCT WIDTH	0.47 in
PRODUCT WEIGHT	0.3 lb
WARRANTY	1 year
COMPLIANCES	CE Marked
CERTIFICATIONS	CSA Certified UL Listed

Product specifications

TYPE	Premium+ Inductive Proximity Sensor
CONTACT RATING	500 mA at 6-30 Vdc
ACTUATOR FUNCTION	Shielded
CABLE TYPE	Polyvinyl Chloride (PVC)
ACCURACY	< 1% sensing range
ENCLOSURE MATERIAL	303 stainless steel
CONTACT CONFIGURATION	NO NPN open collector
SERIES	E57
ENVIRONMENTAL RATING	NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13, IP67, IP69K
CORD LENGTH	79.2 ft
OPERATING TEMPERATURE - MAX	158 °F
OPERATING TEMPERATURE - MIN	-13 °F
MAXIMUM DC CURRENT	500 mA
INPUT VOLTAGE	6-48 Vdc
LED INDICATOR	360 ° viewable LED
PROTECTION	Auto reset

Resources

CATALOGS

[Product Range Catalog](#)
[Sensors – products, basic information, applications](#)

[Sensing Solutions](#),
[Inductive Proximity Sensors, Volume 8, Tab 3](#)

MULTIMEDIA

[We make what matters](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - E57LAL12T110](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

