



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **E57MAL18A2B1 18MM STD Ind Prox 2W Ac Mini Conn** *Eaton Corp*

Catalog Number	E57MAL18A2B1
Manufacturer	Eaton Corp
Description	Inductive Proximity Sensor, E57, Straight, Shielded, 360° Viewable Led, Mini, 250 Ma At 250V, 3 Pin, <3% Sensing Range, PVC, 2-Wire Ac, No, 20-250V
Weight per unit	0.3000 (lbs/each)
Product Category	Inductive Proximity Sensor

### **Features**

Accuracy	< 3% sensing range
connection	Mini
dimensions	3.3900 IN X 0.7100 IN X 0.7100 IN
media	Yes

### **Descriptions**

Description	18MM STD IND PROX 2W AC MINI CONN
extra long description	ETN E57MAL18A2B1 18MM STD IND PROX
Features	E57G general purpose sensors are a cost-effective solution that is optimised to include only those functions that are necessary for basic, reliable sensing without lacking the performance or features you expect in an Eaton product. These sensors include various diameter options designed to fit a variety of applications.
Long Description	Inductive Proximity Sensor, E57, Straight, Shielded, 360° viewable LED, Mini, 250 mA at 250V, 3 pin, <3% sensing range, PVC, 2-wire AC, NO, 20-250V
Product Type	18MM STD Ind Prox 2W Ac Mini Conn

### **Manufacturer Information**

Brand	EATON CUTLER-HAMMER
GTIN	00782113317748
Manufacturers Part Number	E57MAL18A2B1
UPC	782113317748

### **Taxonomies, Classifications, and Categories**

Category Description	SENSORS
Type	Inductive Proximity Sensor

### **Packaging**

Carton	1
Weight Per each	0.3



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Stationary Mach Equip In Factory - Other Stationary Machinery and Equipment - In Factory
environmental conditions	NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13, IP67, IP69K
standard	UL Listed, CSA Certified, CE Marked