

# Eaton EABC26

Catalog Number: EABC26

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, C shape, 3/4"

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover	EABC26
	UPC
	782274247809
Product Length/Depth	Product Height
5.56 in	3.75 in
Product Width	Product Weight
2.78 in	4 lb

[Area classification](#)

Hazardous/Classified Locations

[Standards type](#)

NEC/CEC

[NEC hazardous rating](#)

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

[Material](#)

Feraloy iron alloy

[NEMA Rating](#)

3

4

7

9

[Cover opening diameter](#)

3"

[Trade size](#)

3/4"

[Shape](#)

C

[Catalogs](#)

Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page

[Certification reports](#)

Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification (EAB)

Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification (EAB)

[Installation instructions](#)

IF 1472 - EAB Condulet Conduit Outlet Bodies

IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes

[Specifications and datasheets](#)

Eaton Specification Sheet - EABC26

[Technical service bulletins](#)

Industrial Fittings Bend Radius and Cubic Capacity Chart